

456 Basic Model

Model : A456FBI1, A456NBI1, A456FBS1, A456NBS1.

* : ,

.

1. ()

1- 1. -

.

1- 2. - (Knurl) .
가


. ()

1- 3. ON .

1- 4. ON .

2. ON/ OFF .

2- 1. ON - Probe  .

2- 2. OFF -  4 .
- 1 OFF . (OFF 가 : 5- 3- 9)

3. 0 .

3- 1. ON .
3- 2. 0 .(“ 1”)

3- 3. “ ” 가
(Test Foil) 2- 3 .
(가 .)

:

3- 4. ()가 가 .

3- 5. ,
.

(“ 2”)

3- 6. “ ” 가

2-3

3-7.

3-8. ON

가

4.

- 456 Basic

4-1.

4-2.

4-2-1.

-

4-2-2.

-

4-2-3.

-

4-2-4.

- F N

4-2-5.

- η :

- :

- :

- $>$:

- $<$:

*

5.

-

5-1. / -

()

5-2.

-

5-3.

-

5-3-1.

-

5-3-2.

-

(4

)

5-3-3.

-

. (“ ” 가 .)

5-3-4.

-

5-3-5.

-

(μm , mm, mil, thou, inch 가)

- 5-3-6. - () “ ” “ ” 가 가 . (가 .)
- 5-3-7. - 0-5 가 .
- 5-3-8. - .
- 5-3-9. - OFF
- 5-3-10. - ON .
- 5-4. - 3가 가 .
- 5-4-1. - .
- 5-4-2. - .
- 5-4-3. - .
- 5-5. - .